



## ExTender™ Web Lanyards Instruction/Specification Manual 2025

ENGLISH  
VERSION

### !WARNING TO USER!

You are required to read and use the Instruction/Specification manual supplied at the time this device was shipped. Improper use and installation can result in serious injury or death. Follow inspection requirements before each use.

### Material Specification

**Webbing:** 2" wide polyester

**Min. Tensile Strength:** 10,000lb(45kN)

**Max User wt.:** One person 310lb(140kg) including tools and equipment

**Service Length:** Approx. 18"

**Connectors:** Snaphook / carbiners 3,600lb(16kN) gate strength

**Connector Compliance:** ANSI Z359.12-09/CSA Z259.12-16

**ExTender Compliance:** ANSI Z359.1-07/OSHA 1926.502

\*"Qualified or Competent Person" see OSHA definition.

ⓧ=Inspection Points

### Specified Use

Provides easy access to connect/disconnect PPE to the dorsal D-ring of a full body harness. See Figs.1,2,4 and 5.

### Energy Absorber (E/A) Requirement

ExTender lanyards are static and do not absorb shock. Equipment attached to the ExTender must include a personal E/A or a Class 1 SRL or Class 2 SRL-LE. See Figs.4,5. **Attaching a personal E/A directly to an ExTender lanyard must be approved by a competent person.\***

### Non-Specified Use

Do not attach ExTender lanyards to a harness side D-ring.

### Dee-Loop Models

Dee-Loops are best suited for applications where the lanyard is not required to be removed frequently. Follow instructions shown at Figs. 3.0, 3.1, 3.2.

### Fall Protection Specification

**Fall Arrest:** PPE must include an E/A as shown at Figs.4 and 5.

**Fall Restraint:** Use as a connecting lanyard with a rope grab device provided there is no exposure to a free fall.

Table 1 Dee-Loop ExTenders

Part No.	B End	▲Length
6002-D	Small D-ring	19"
6002-DC	△Carabiner	22"
6002-DL	Web Loop	18"
6002-DS	Snaphook	23"
6002-DCC	▲Carabiner	22"

△Anodized aluminum carabiner.

▲Captive non-removable aluminum carabiner.

▲Service length attached to harness dorsal D-ring.

Table 2 Snaphook/Carabiner ExTenders

Part No.	A End	B End	Length
6002-C	△Carabiner	Small D-ring	18"
6002-CL		Web Loop	17"
6002-CC	▲Carabiner	▲Carabiner	22"
6002-S	Snaphook	Small D-ring	19"
6002-SL		Web Loop	18"
6002-SS		Snaphook	22"

Fig.1

### ExTender Attachment Full Body Harness



### ExTenders w/Snaphook/Carabiner Connectors

6002-C

6002-CL

6002-CC

Twist Lock Carabiner

6

Service Length Measured From A End to B End

Small D-ring

7

Web Loop

4

5

Captive Carabiner

6

6002-S

6002-SL

6002-SS


Snaphook

6

Fig.2 ExTender Attachment

Full Body Harness

### Dee-Loop™ ExTender Lanyards



### Dee-Loop Attachment

Fig.3.0  
Feed Dee-Loop Thru D-ring and Fold Down

Fig.3.1  
Feed Webbing Thru Dee-Loop

Fig.3.2  
Cinch Dee-Loop Tightly

Red Tracer Faces Out